

DELO-KATIOBOND® 4552

Light-activated adhesive, low viscos

Base

- modified epoxy resin
- one-component, solvent-free, light-activated

Use

- especially for rigid bondings and sealings for example of relays and switches
- for the bonding of metal, glass, plastic and other materials as well as for the coating, fixing or sealing of electronic components
- also suitable for the bonding of opaque components through preactivation
- the product is normally used in a temperature range of -40 °C to +150 °C; depending on the application, other limits may be more reasonable
- positively tested according to UL 94 HB
- compliant with RoHS directive 2002/95/EC

Processing


- the adhesive is supplied ready for use; in case of cool storage, it must be ensured that the container is conditioned to room temperature before use
- the containers are conditioned at room temperature (max. 25 °C); additional heat addition is not allowed
- the adhesive is usually applied by dispensing
- the adhesive can be processed well from the original container or with DELO dispensing units
- the surfaces to be bonded must be dry as well as free of dust, grease and other contaminations
- use DELOTHEN cleaners for the cleaning of bonding surfaces
- when using aqueous cleaners with alkaline properties, they must be removed from the bonding surface after cleaning through appropriate rinsing cycles
- dispensing valves and product-bearing elements must be carefully cleaned before use, residues of other products must totally be completely removed; DELOTHEN EP as well as acetone, isopropanol or a mixture of both are recommended to remove DELO-KATIOBOND residues
- for further information please refer to our instructions for use DELO-KATIOBOND

Curing

- curing or activation with visible light in a recommended wavelength range of 400 - 550 nm
- the cationic curing mechanism enables adhesive curing after the joining of opaque components after sufficient irradiation
- after irradiation curing until final strength within 24 h at room temperature
- increased temperatures accelerate the reaction, lower temperature decelerate it
- increased intensities shorten the required irradiation time, lower intensities prolong it

Absorption spectrum

- photoinitiation system in epoxy resin basic matrix



Curing parameters

- dependent on material thickness and absorption, adhesive layer thickness, lamp type and distance between lamp and adhesive layer

Technical data

Color cured in a layer thickness of approx. 1 mm	brown clear
Density [g/cm³] DELO Standard 13 at room temperature (approx. 23 °C)	1.1
Viscosity [mPas] at 23 °C, Brookfield spm 3/10	1200
Preactivation time [s] DELO Standard 19 DELOLUX 03 S, UVA intensity: 55 - 60 mW/cm ² DELOLUXcontrol	3
Open time after preactivation [s] DELO Standard 19 at room temperature (approx. 23 °C) and normal room lighting	20
Minimal irradiation time [s] DELO Standard 37, DSC UVA intensity: 55 - 60 mW/cm ² DELOLUXcontrol, at 30 °C	15
Recommended irradiation time [s] DELOLUX 03 S, UVA intensity: 55 - 60 mW/cm ² DELOLUXcontrol	60
Curing time until final strength [h] at room temperature (approx. 23 °C) after irradiation	24
Compression shear strength glass/glass [MPa] DELO Standard 5 UVA intensity: 55 - 60 mW/cm ² , DELOLUXcontrol, irradiation time: 60 s curing time: 24 h at room temperature (approx. 23 °C)	24
Compression shear strength glass/Al [MPa] DELO Standard 5 UVA intensity: 55 - 60 mW/cm ² , DELOLUXcontrol, irradiation time: 60 s curing time: 24 h at room temperature (approx. 23 °C)	17
Compression shear strength glass/FR4 [MPa] DELO Standard 5 UVA intensity: 55 - 60 mW/cm ² , DELOLUXcontrol, irradiation time: 60 s curing time: 24 h at room temperature (approx. 23 °C)	27

Compression shear strength PC/Al [MPa] DELO Standard 5 UVA intensity: 55 - 60 mW/cm ² , DELOLUXcontrol, irradiation time: 60 s curing time: 24 h at room temperature (approx. 23 °C)	6
Compression shear strength PC/PC [MPa] DELO Standard 5 UVA intensity: 55 - 60 mW/cm ² , DELOLUXcontrol, irradiation time: 60 s curing time: 24 h at room temperature (approx. 23 °C)	30
Compression shear strength PMMA/PMMA [MPa] DELO Standard 5 UVA intensity: 55 - 60 mW/cm ² , DELOLUXcontrol, irradiation time: 60 s curing: 24 h at room temperature (approx. 23 °C)	10
Compression shear strength PBT/PBT [MPa] DELO Standard 5 UVA intensity: 55 - 60 mW/cm ² DELOLUXcontrol, at optimal preactivation time curing time: 24 h at room temperature (approx. 23 °C)	6
Compression shear strength PETP/PETP [MPa] DELO Standard 5 UVA intensity: 55 - 60 mW/cm ² DELOLUXcontrol, at optimal preactivation time curing time: 24 h at room temperature (approx. 23 °C)	8
Tensile strength [MPa] DIN EN ISO 527	24
Elongation at tear [%] DIN EN ISO 527	3
Young's modulus [MPa] DIN EN ISO 527	1100
Shore hardness D according to DIN EN ISO 868	58
Decomposition temperature [°C] DELO Standard 36	257
Glass transition temperature [°C] rheometer	130
Coefficient of linear expansion [ppm/K] TMA, in a temperature range of +30 to +150 °C	158
Shrinkage [vol. %] DELO Standard 13	3.7
Water absorption [weight %] according to DIN EN ISO 62, 24 h at room temperature (approx. 23 °C)	1.5
Specific volume resistance [Ωcm] VDE 0303, part 3	>1xE13
Surface resistance [Ω] VDE 0303, part 3	>1xE13
Dielectric strength [kV/mm] VDE 0303, part 2	18
Dielectric constant RF-IV method, 1 MHz, at 25 °C +/- 3 °C	3.9
Dielectric constant RF-IV method, 10 MHz, at 25 °C +/- 3 °C	3.7
Dielectric constant RF-IV method, 100 MHz, at 25 °C +/- 3 °C	3.5

Dielectric constant

RF-IV method, 1 GHz, at 25 °C +/- 3 °C

3.2

Creep resistance CTI

VDE 0303, part 1, IEC 112

600 M


Storage life at room temperature (max. 25 °C)

in unopened original container


6 months

Performance under temperature influence


compression/shear strength glass/glass after temperature storage based on initial value at room temperature measured at room temperature (approx. 23 °C) according to DELO standard 5




compression/shear strength glass/glass at temperature based on initial value at room temperature measured at determined temperature according to DELO standard 5




Young's modulus after temperature storage based on initial value at room temperature measured at room temperature (approx. 23 °C) according to DIN EN 527, test specimen type 1B, thickness 2 mm



tensile strength after temperature storage based on initial value at room temperature measured at room temperature (approx. 23 °C) according to DIN EN 527, test specimen type 1B, thickness 2 mm



elongation at tear after temperature storage based on absolute initial value at room temperature measured at room temperature (approx. 23 °C) according to DIN EN 527, test specimen type 1B, thickness 2 mm



Performance under chemical influence

compression shear strength after storage for 1,000 h
based on initial value at room temperature
measured at room temperature (approx. 23 °C)
according to DELO Standard 5

Chemical medium	Compression/shear strength glass/Al [%]
acetone	83
ethanol denatured	97
ATF gear oil	106
petrol	92
diesel fuel	80
engine oil 10W40	129
demineralised water / glykol mixture 50:50	74

Instructions and advice

General

The data and information provided are based on tests performed under laboratory conditions. Reliable information about the behavior of the product under practical conditions and its suitability for a specific purpose cannot be concluded from this.

Many product properties are subject to temperature and may change permanently, especially at high temperatures.

It is the user's responsibility to test the suitability of the product for the intended purpose and temperature range of use by considering all specific requirements. Type and physical and chemical properties of the materials to be processed with the product, as well as all actual influences occurring during transport, storage, processing and use, may cause deviations in the behavior of the product compared to its behavior under laboratory conditions. All data provided are typical average values or uniquely determined parameters measured under laboratory conditions.

The data and information provided are, therefore, no guarantee for specific product properties or the suitability of the product for a specific purpose.

Instructions for use

The instructions for use of DELO-KATIOBOND are available on: www.DELO.de. We will be pleased to send them to you on demand.

Occupational health and safety

see material safety data sheet

Specification

see quality assurance test report